## Stella Discoverer STJW159

_			٠.	
( :\	m	$n \cap$	SIT	ion
$\sim$		$\sim$	$\circ$	

94% recycled polyester 6% elastane

## Printing guide

Screen print	• • •	Waterbase / Plastisol Need special inks for low curing temperature.	
Discharge	000	Not applicable	
Transfer -DTF, Flock, Flex, Screen Transfer,	•••	Use type of glue adequate for max 130°C. Steam after press to limit shyny marks.	
Direct To Garment	000	Not applicable	
Embroidery	•••	Direct embroidery, stitched patch, loop labels	
Sublimation	000	Not applicable	